

# Bells

## Single Stroke

### 330EX Series

Edwards 330EX Series single stroke bells produce a clearly defined note for timing, scheduling, paging and general alarm applications. Coded, intermittent current may be used to cause the striker to gong, pause and strike again for any specified period of time. Designed for use in hazardous locations, they have a NEMA Type 4 housing.

### Features and Specifications

- Single stroke or coded intermittent stroke
- Completely assembled
- Sealing fitting for 3/4" (19mm) conduit and wire leads for power connections
- Mounts directly on surface
- Self-compensating solenoid plunger
- Low power drain for efficient operation over long wire runs
- Available with 6" or 10" gongs
- Corrosion resistant heat flowed epoxy finish
- Suitable for use in outdoor applications
- NEMA Type 4 housing
- UL Listed for Class I, Divisions 1 and 2, Groups B, C & D; Class II, Divisions 1 and 2, Groups E, F & G; and Class III




### Ordering Information

Description	Cat. No.	Operating Voltage <sup>1</sup>	Current <sup>2</sup>	Gong Size	dB at 1m/10ft.
AC Single Stroke	<b>332EX-6N5</b>	120V AC	0.43 A	6" (152mm)	96/86
	<b>332EX-10N5</b>	120V AC	0.43 A	10" (254mm)	104/94
	<b>332EX-6R5</b>	240V AC	0.20 A	6" (152mm)	96/86
	<b>332EX-10R5</b>	240V AC	0.20 A	10" (254mm)	104/94
DC Single Stroke	<b>333EX-6G1</b>	24V DC	3.50 A	6" (152mm)	96/86
	<b>333EX-10G1</b>	24V DC	3.50 A	10" (254mm)	104/94
	<b>333EX-6P1</b>	125V DC	0.52 A	6" (152mm)	96/86

<sup>1</sup>AC voltage frequency is 50/60 Hz.

<sup>2</sup>Single pulse duration - 8 to 16 milliseconds



# Bells

## Single Stroke

### 330EX Series

#### Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Gong Size	Dimensions		
				A	B	C
332EX-6N5	5.70	7.50	6" (152mm)	4 1/16" (103mm)	4 13/16" (122mm)	5/8" (16mm)
332EX-6R5	5.70	7.50	6" (152mm)	4 1/16" (103mm)	4 13/16" (122mm)	5/8" (16mm)
332EX-10N5	8.54	9.78	10" (254mm)	6 1/16" (154mm)	5 3/8" (137mm)	2 5/8" (67mm)
332EX-10R5	8.54	9.78	10" (254mm)	6 1/16" (154mm)	5 3/8" (137mm)	2 5/8" (67mm)
333EX-6G1	5.70	7.50	6" (152mm)	4 1/16" (103mm)	4 13/16" (122mm)	5/8" (16mm)
333EX-6P1	5.70	7.50	6" (152mm)	4 1/16" (103mm)	4 13/16" (122mm)	5/8" (16mm)
333EX-10G1	8.54	9.78	10" (254mm)	6 1/16" (154mm)	5 3/8" (137mm)	2 5/8" (67mm)

