

# Intercoms

## Industrial

### 5570 Series

The Edwards 5570M intercom is a heavy-duty UL and cUL listed signal appliance designed for use in industrial and hazardous location applications.

The 5570M can be configured by means of a slide switch. The AC line has a 1/2 amp 250-volt type GMC fuse. Operating selections include balanced or unbalanced line operation and modes of Master or Satellite can be selected.

The unit features a transformer isolated audio input and a choice of one of four selectable alert tones. For indoor applications where ambient noise is high, a hand-held noise cancelling microphone kit is available.

### Features and Specifications

- Suitable for use in indoor and outdoor hazardous locations
- Balanced or unbalanced line operation
- Master or satellite modes
- Four selectable alert tones
- Marine rated
- UL Class 1, Div. 2, Groups A, B, C and D
- Operating temperature range: -31°F to 150°F (-35°C to 66°C)



### Ordering Information

Description	Cat. No.	Operating Voltage <sup>1</sup>	Current		Frequency Response (-6dB)	Input Impedance	Speaker Rating	Speaker Impedance
			Standby	Tone On				
Hazardous Location Intercoms	<b>5570M-AQ</b>	24V AC/DC	0.321/0.111 A	1.29/0.64 A	150 Hz to 12 KHz	15K Ohms	30 Watts	16 Ohms
	<b>5570M-NR5</b>	120V AC/240V AC	0.075/0.037 A	0.188/0.073 A	150 Hz to 12 KHz	15K Ohms	30 Watts	16 Ohms

<sup>1</sup>AC voltage frequency is 50/60 Hz

### Accessories

Description	Cat. No.
Hand-held Noise Cancelling Microphone Kit	<b>5570MIC</b>
Microphone Outdoor Application Kit	<b>5542WPK</b>



# Intercoms Industrial 5570 Series

## Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
5570M-AQ	12.13	12.50
5570M-NR5	12.13	12.50
5570MIC	1.00	1.25
5542WPK	0.42	0.70

