

# Beacons

## Flashing Xenon

### 3000 Series

The 3000 Series beacons are surface, flange mounted strobes designed for industrial applications and for applications where warning on a moving vehicle, such as a fork lift or tow motor is required.

The unit draws low current for a 12-48 V DC unit. The twist on-off lens makes for easy strobe tube and/or lens replacement. The 3000 Series beacons also feature a fully gasketed lens.

### Features and Specifications

- Xenon light source
- 1.5 Joule Strobe
- 80 Nominal Single Flashes per minute (fpm)
- Flange mount
- 18" wire leads
- Low current draw
- 150,000 peak candela



5"



### Ordering Information

Description	Cat. No.	Operating Voltage	Current	Lens Colors	Replacement	
					Lens	Strobe Tube
Flashing Beacon	3000SDR-EK	12-48V DC	0.275 A - 0.130 A	Red	3000LM-R	91B-ST
	3000SDA-EK	12-48V DC	0.275 A - 0.130 A	Amber	3000LM-A	91B-ST
	3000SDB-EK	12-48V DC	0.275 A - 0.130 A	Blue	3000LM-B	91B-ST
	3000SDG-EK	12-48V DC	0.275 A - 0.130 A	Green	3000LM-G	91B-ST
	3000SDC-EK	12-48V DC	0.275 A - 0.130 A	Clear	3000LM-C	91B-ST

### Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
3000SDR-EK	0.57	0.72
3000SDA-EK	0.57	0.72
3000SDB-EK	0.57	0.72
3000SDG-EK	0.57	0.72
3000SDC-EK	0.57	0.72

