




EWCE-Series Electric Wire and Cable Cutters

EWCE-Series Electric Wire and Cable Cutters combine the efficiency and safety of their hydraulic counterparts with the greater portability of electric tools.

Their lighter weight allows for easier carrying and positioning. Available in 120V and 230V versions.

- ① Durable, guillotine-style blades maintain effectiveness throughout rigorous use.
- ② Cutting head opens wide for easy positioning of wire or cable.
- ③ Robust handles enable easy positioning and transport.
- ④ Double-acting cylinder with directional control improves handling and reduces jamming.



◀ Cut through wire rope and cables with ease.

EWCE Series



Maximum Material Hardness:

HRc 48

Maximum Material Diameter:

42 - 55 mm

Voltage*:


120 and 230 V

* ETL certification applies to 120 Volt tools only.

Voltage: (Model Number ending with suffix)

B = 120V, 60 Hz (with American-style NEMA 1-15 plug)

E = 230V, 50 Hz (with European-style SCHUKO plug)



| Maximum Material Diameter* (mm) | | Power Specifications | | | | Model Number | Maximum Material Hardness* (HRc) | Maximum Cutting Force (kN) | Dimensions (mm) | | | | Cord Length (m) | Replacement Blade Kit Model Number | |
|---------------------------------|-----------|----------------------|----|------|-----|----------------|----------------------------------|----------------------------|-----------------|-----|-----|----|-----------------|------------------------------------|------------------|
| Electric Cable | Wire Rope | Volt | Hz | Amps | kW | | | | A | B | C | D | | | |
| 55 | 42 | 120 | 60 | 11 | 1,3 | EWCE55B | 48 | 380 | 627 | 183 | 264 | 56 | 1,8 | 25 | EWCE5501K |
| 55 | 42 | 230 | 50 | 6,8 | 1,4 | EWCE55E | 48 | 380 | 627 | 183 | 264 | 56 | 3,0 | 25 | EWCE5501K |

* Maximum material properties indicated refer to the material to be cut.