

# Pumps & Accessories for EDCH-Cutters



## Pumps & Accessories for EDCH-Cutters

The EDCH-Decommissioning Cutters are designed to work in a wide variety of environments, from factories to demolition projects.

Enerpac offers multiple pump options to provide power, speed and mobility for all your applications.

## ZC ZE Series



Reservoir Capacity:

**4,6 - 9,8 litres**

Motor Size:

**1,0 - 1,1 - 5,6 kW**

Maximum Operating Pressure:

**700 bar**



### ZC3-Series Cordless Pumps

Specialized **ZC3-Series** Cordless Pumps offer the portability of a cordless tool without the added weight of an integrated motor, combining freedom of movement with ease of use. Recommended for use with the **EDCH130** cutter.



### ZE4-Series Pumps

Specialized **ZE4-Series** Pumps provide a balance of speed and versatility. Recommended for use with all **EDCH** cutters when the convenience of using standard voltage is required.



### ZE6-Series Pumps

Specialized **ZE6-Series** pumps offer a high-flow rate that provides fast performance. Recommended for use with all **EDCH** cutters when 3-phase power is available, and speed is critical.



### Optional Gauge Kit GKHC

Optional gauge and accessories can be used to monitor pressure in the hydraulic system. Enerpac recommends **GKHC Gauge Kit** for use with Enerpac hydraulic cutters.



### Twin Hose

EDCH-Series Cutters require a twin hose for operation. The hose comes equipped with the appropriate couplers.

| Description                         | Model Number   |
|-------------------------------------|----------------|
| 6,1 m long, twin hose with couplers | <b>CH720MC</b> |

### Pump Voltage 1-phase: (Model Number ending with suffix)

**B** = 120V, 60 Hz (with American-style NEMA 5-15 plug);

**E** = 230V, 50 Hz (with European-style SCHUKO plug); **I** = 230V, 50 Hz (with NEMA 6-15 plug)

| Pump Series       | Pump Model Number * | Motor Electrical Specifications<br>(Volt - Phase, Hz) | Motor Size<br>(kW) | Reservoir Capacity<br>(litres) | Dimensions (mm) |        |       | Weight (kg) | Required Twin Hose Model Number<br>(Sold separately) | Compatible Cutter Model Number<br>(Sold Separately) |
|-------------------|---------------------|---|--------------------|--------------------------------|-----------------|--------|-------|-------------|--|---|
|                   |                     |   |                    |                                | Height          | Length | Width |             |  |   |
| ZC3               | <b>ZC3204XB</b>     | <b>Cordless</b> (115 V Charger 60 Hz)                 | 1,0                | 4,6                            | 653             | 472    | 363   | 27          | <b>CH720MC</b>                                       | <b>EDCH130</b>                                      |
|                   | <b>ZC3204XE</b>     | <b>Cordless</b> (230 V Charger 50 Hz)                 |                    |                                |                 |        |       |             |  |   |
| ZE4               | <b>ZE4204XB</b>     | 115 V - 1 ph, 50-60 Hz                                | 1,1                | 4,6                            | 513             | 521    | 279   | 45          | <b>CH720MC</b>                                       | <b>EDCH130</b><br><b>EDCH145</b><br><b>EDCH170</b>  |
|                   | <b>ZE4204XE</b>     | 208-240 V - 1 ph, 50-60 Hz                            |                    |                                |                 |        |       |             |  |   |
|                   | <b>ZE4204XI</b>     | 208-240 V - 1 ph, 50-60 Hz                            |                    |                                |                 |        |       |             |  |   |
| ZE6 <sup>1)</sup> | <b>ZE6210XG-S</b>   | 208-240 V - 3 ph                                      | 5,6                | 9,8                            | 384             | 559    | 384   | 77          | <b>CH720MC</b>                                       | <b>EDCH130</b><br><b>EDCH145</b><br><b>EDCH170</b>  |
|                   | <b>ZE6210XJ-S</b>   | 460-480 V - 3 ph                                      |                    |                                |                 |        |       |             |  |   |
|                   | <b>ZE6210XK-S</b>   | 440 V - 3 ph  |                    |                                |                 |        |       |             |  |   |
|                   | <b>ZE6210XW-S</b>   | 380-415V - 3 ph                                       |                    |                                |                 |        |       |             |  |   |

\* Indicated pumps come equipped with appropriate configurations to work with indicated cutters.

<sup>1)</sup> ZE6 pumps are available with roll cages. To add a roll cage, add an "R" prior to the "S" in the model number: example **ZE6410XG-RS**.