

ERIEZ HYDROFLOW®

Drum Top Coolant Mixers

84-1000E & 84-1020

Eriez HydroFlow Drum Top coolant mixers are designed to be used with any water soluble coolant with a viscosity of 400 SUS or less. These rugged units use a needle valve to set the coolant ratio, allowing these units to mix much richer than the fixed orifice style units. Simple to use and with all metal construction will give years of reliable use.

There are two models:

84-1000E Drum Top 3 Gallon Per Minute (11 liters/minute) Venturi Mixer with a mixing ratio range of 2%-20%.

Includes installation kit (kit includes swivel garden hose adapter and discharge hose).

84-1020 Drum Top 10 Gallon Per Minute (38 liters/minute) Venturi Mixer with a mixing ratio range of 2%-20%.

Includes installation kit (kit includes swivel garden hose adapter and discharge hose).

**Utility Requirements:**

Water: 25 PSI minimum (.5 bar) running, 1/2" pipe (13mm)

World Authority in Separation Technologies

Headquarters: 2200 Asbury Road, Erie, PA 16506-1402 U.S.A.

Telephone: 814-835-6000 • 800-345-4946 • Fax: 814-838-4960

International Fax: 814-833-3348

Web Site: <http://www.eriez.com> e-mail: eriez@eriez.com

Manufacturing Facilities: AUSTRALIA • BRAZIL • CANADA • CHINA • INDIA • JAPAN • MEXICO • SOUTH AFRICA • UNITED KINGDOM • UNITED STATES



HYDROFLOW®
FILTRATION SYSTEMS