

FRD 16-8 Rect. Inline Fan

16x8" rectangular inline duct fan w/metal housing, 120V, 1~

Item #: 40031

Variant: 115V 1~ 60Hz



This rectangular, centrifugal inline duct fan is ideal for areas with limited space and large ventilation needs such as multi-family or commercial buildings.

- Hinged access door for easy service access
- Quick access to exterior mount terminal box
- Mount the fan at any angle/direction within the ductwork
- Built-in thermal overload protection with automatic reset
- Operable in airstream temperatures up to 140°F
- CSA, UL, and AMCA Air & Sound certified
- Five-year warranty

The compact housing design of the 16-8 FRD series fan allows for installation directly within 16" x 8" rectangular ductwork, without the need for large elbows or transitional sections. The 16-8 FRD series fan is simple to install with no extra materials required.

