

XC-Series, Cordless Torque Wrench Pumps



Battery-Powered Torque Wrench Pumps

The XC-Series Cordless Torque Wrench pump is ideal for applications in the PowerGen, Oil & Gas and MRO markets. This portable pump is perfect for remote locations, sites that do not have access to power or where trip hazards are a concern.

The interactive pendant allows the user to set and clear pressure and operate in manual or auto-cycle mode. The pump has an easily accessible user adjustable valve for precise pressure control.

| Torque Wrench Model | Nut A/F (mm) | Stud (mm) | Pressure (bar) | Torque (Nm) | Fasteners torqued |
|---------------------|--------------|-----------|----------------|-------------|-------------------|
| S3000X | 60 | 38 | 330 | 2035 | 32 |
| W2000X | 60 | 38 | 350 | 1356 | 52 |

XC Series




Reservoir Capacity:
2,0 litres

Flow at Rated Pressure:
0,25 l/min

Motor Size:
0,37 kW



Maximum Operating Pressure:
700 bar



Torque Wrench Hoses

Use Enerpac 700 bar THQ-Series torque wrench hoses with torque wrenches and pumps. See page 257.

| | |
|--------------------|----------------|
| 2 m long, 2 hoses | THQ702T |
| 6 m long, 2 hoses | THQ706T |
| 12 m long, 2 hoses | THQ712T |



SELECTION CHART

| Description | Useable Oil Capacity (litres) | Model Number | Output Flow Rate (l/min) | | | Included with pump | Weight (kg) ¹⁾ |
|-------------------|-------------------------------|-----------------|--------------------------|---------|---------|------------------------------|---------------------------|
| | | | No Load | 140 bar | 700 bar | | |
| Cordless Pump Kit | 2,0 | XC1502TB | 2,05 | 0,49 | 0,25 | 2 batteries and 115V charger | 12 |
| Cordless Pump Kit | 2,0 | XC1502TE | 2,05 | 0,49 | 0,25 | 2 batteries and 230V charger | 12 |
| Cordless Pump | 2,0 | XC1502T | 2,05 | 0,49 | 0,25 | No batteries or charger | 12 |

¹⁾ Weight includes oil, without battery. Battery weight 1,1 kg.