

# STEEL HANDTRUCKS



## MHS SERIES

Capacity to 500 lbs.

### FEATURES

- ☑ Robotic welded for greater consistency
- ☑ Green epoxy powder coated for a longer lasting finish
- ☑ Back lip on nose plate adds strength, while holding small loads in place
- ☑ Large 8" x 14" nose plate with Super Slik™ raised runners to help slide load on and off with minimal effort
- ☑ Curved crossbars hold load in place



MHS-111-8PN



MHS-112-8PN



MHS-113-8PN



*The*  
**Fairbanks® Company**

*Since 1830*

Copyright© 2007  
All rights reserved

Part No.	Handle Style	Load Capacity	Height	Ship Weight	Wheel Order No.
MHS-113-8PN	Loop	500	46	21	SP8-SC
MHS-112-8PN	Double	500	47	20	
MHS-111-8PN	Continuous	500	45	20	



## TRASH CONTAINER

Capacity to 250 lbs.


The answer to light applications. The center chime hook and curved cross straps securely hold round containers such as small drums, barrels and garbage cans. The 16" wide, 1" x 16-gauge tubular frame is also ideal for wider cartons. The rear handle brace protects handle when in horizontal position. Furnished with 5" x 1-1/2" solid rubber wheels only. Green epoxy powder coated. All-welded construction.



Trash Container Truck						
Part No.	Load Capacity	Height	Width	Ship Weight	Wheel Type	Nose Plate
B-3079-5SR	250	45	16	20	Soft Rubber	6 x 14



## STEEL HANDTRUCK ACCESSORIES



### Folding Nose Extension

For all A1448, C114, C118, C115, and C116 steel handtrucks.  
(Not for CVN 1500) Model No. 26-3-FN, Ship weight 6 lbs. Size: 12" x 26"

### "D" Axle

Fits all 800 lb. capacity industrial steel handtrucks including the CVN1500 2-in-1 truck. Model No. A-1448-D, Ship weight 1.7 lbs.