

prioAir® 6 Inline Duct Fan

6" inline duct fan w/plastic housing, 120V, 1~

Item #: 49310

Variant: 120V 1~ 60Hz



This multi-purpose, high-efficiency inline duct fan moves high volumes of air with low energy. Ideal for long ventilation ducts in low static pressure settings.

- High efficacy (cfm/W) ratio
- Ideal fit for false or drop ceilings
- Indoor & outdoor use
- 100% leak-free fan
- Built-in thermal overload protection with automatic reset
- Operable in air temperatures up to 131°F
- AMCA air & sound certified
- Low ambient noise for quieter operation
- Quick & easy installation
- Mounting bracket included
- Five-year factory warranty

The optimized shape of the aerodynamic optimized impeller provides an ideal air stream. The motor bearings are permanently sealed and self-lubricating for maintenance-free life. With the motor in the airstream, the fan provides the constant dissipation of heat build-up that gives this fan best-in-class longevity and reliability backed by an industry leading warranty.

General application examples for the prio **AIR** fan include supply or exhaust air duct systems in commercial buildings, schools, gymnasiums, commercial bathrooms, manufacturing facilities with extended ductwork, residential attached garages, extra-long duct boosting needs, and crawlspaces.

