

Rn2 Inline Radon Fan

4.5" pipe, plastic housing, 2.0" max SP

Item #: 89052

Variant: 120V 1~ 60Hz



Rn2 Radon Fan is designed for active radon mitigation systems to employ for applications where medium suction and low flow are needed. It is a perfect choice for medium Radon levels and moderate sub-slab communication. Rn2 replaces HP175, HP190, and HP2190 models.

- Designed specifically for Active Soil Depressurization (ASD) mitigation applications
- Medium suction, low flow
- For residential applications
- Air-tight housing - zero leakage
- UV resistant plastic housing
- UL Listed for safety and outdoor use
- HVI certified fan performance
- 5-year factory warranty

Manufactured from two molded plastic pieces seamlessly joined. It is inherently and permanently airtight ensuring no Radon gas leakage. A large watertight electrical wiring enclosure ensures electrical installation quick and simple. Fan motor is thermal overload protected with automatic reset and can be installed both indoors or outdoors. To simplify installation on a 3" or 4" PVC pipe, use FRIK 4x3 or FRIK 4x4 Installation kits.

