

FRD 24-14 Rect. Inline Fan

24x14" rectangular inline duct fan w/metal housing, 120V, 1~

Item #: 40115

Variant: 115V 1~ 60Hz



This rectangular, centrifugal exhaust/supply series inline duct is ideal for buildings with limited space and large ventilation needs. Application examples include commercial and residential structures such as hospitals, schools, or office buildings.

- Hinged access door for easy service access
- Quick access to exterior mount terminal box
- Mount the fan at any angle/direction within the ductwork
- Built-in thermal overload protection with automatic reset
- Operable in airstream temperatures up to 140°F
- CSA, UL, and AMCA Air & Sound certified
- Five-year warranty

The compact housing design of the 24-14 FRD series fan allows for installation directly within 24" x 14" rectangular ductwork, without the need for large elbows or transitional sections. The 24-14 FRD series fan is simple to install with no extra materials required.

