

PRO 80 Exhaust Fan

Bath Fan, Surface Mount, 1 Grille, 80 cfm, 4" Duct

Item #: 98500



- 1.2 Sones
- Built-in backdraft damper
- High efficiency motor
- 3 year warranty

Application

The PRO 80 exhaust fan provides remarkably quiet, energy efficient ventilation for bathrooms, powder rooms and other areas with square footage up to 130 sq. ft. The fans are designed for intermittent or continuous operation to meet ASHRAE Standard 62.2.

Model

80 cfm fan with a ceiling grille and damper. Uses a 4" flexible duct. The PRO80 fan has a unique plug and play concept that allows you to add accessories such as a humidity sensor without changing the fan. The product is provided with an adjustable 12-24" bar hanger for ease of installation.

This model holds an ETL listing and conforms to UL and CSA safety standards. ENERGY STAR® and HVI qualified, California Title 24 Listed

