

# SHR 1200 Heat Rec Ventilator

Side duct connection HRV, 1218 cfm

Item #: 99272

Variant: 120V 1~ 60Hz



- Airflow up to 1219 cfm @ 0.4" PS
- Push-pull configuration
- Removable screw terminal for easy connection
- Dual service doors & reversible electrical box
- External three position switch (Low/Standby/High)

## Application

The SHR 1200 Commercial Heat Recovery Ventilation system (HRV) complements today's tight buildings.

## How it works

Fantech Heat Recovery Ventilators (HRV) are designed to supply air into a building while exhausting an equal amount of contaminated air to the outside. The aluminum heat exchanger core transfers sensible energy between air streams resulting in tempering of the supply air and reduced loads on the HVAC system.

## Defrost cycle

A preset defrost sequence is activated at an outdoor air temperature of 23°F and lower. During the defrost sequence, the supply blower shuts down & the exhaust blower switches to high speed to maximize the effectiveness of the defrost strategy. The unit then returns to normal operation, and continues the cycle.

