

**F23X**

**STEP DRILL BITS**

For creating and enlarging holes in sheet metal, with interchangeable point.



starting from  
**€ 53,30**



Stem	Ø	Art.	€	Promo
10 mm	2,5 ÷ 32 (2,5-6,3-11,2-14,5-18,2-22,3-27,9-32) mm	F232	€ 72,40	€ 53,30
10 mm	2,5 ÷ 38 (2,5-6,3-13-16-19-21-23-26-29-32-35-38) mm	F238	€ 77,50	€ 56,80

**F001/10**


€ 228,00

**SET FRONTAL ROUGHING END MILLS**

DIN 844/B, regular length, center cutting, weldon shank.



**€ 166,00**



Mill	Ø	Stem
	6   8   10   12   14   16   18   20   22   25 mm	6   10   10   12   12   16   16   20   20   25 mm

**F001/20**

€ 228,00

**SET END MILLS**

DIN 844/B and DIN 327/D, two and four flute, regular length, weldon shank, center cutting.



**€ 157,00**



2 Flute mill	Ø 3 - 4 - 5 - 6 - 8 - 10 - 12 - 14 - 18 - 20 mm
Stem	Ø 6 - 6 - 6 - 6 - 10 - 10 - 12 - 12 - 16 - 20 mm
4 Flute mill	Ø 3 - 4 - 5 - 6 - 8 - 10 - 12 - 14 - 18 - 20 mm
Stem	Ø 6 - 6 - 6 - 6 - 10 - 10 - 12 - 12 - 16 - 20 mm

**F008DC**

€ 64,30

**HARD METAL ROTARY BURR SET**

With diamond cut.



**€ 50,00**



Sizes	10 x 20 mm
Type	B, C, D, G, M
Stem	6 mm

**F008SC**

€ 64,30

**HARD METAL ROTARY BURR SET**

With single cut.



**€ 50,00**



Sizes	10 x 20 mm
Type	B, C, D, G, M
Stem	6 mm

**F008-**

**CARBIDE ROTARY FILE SET**

Cross cut



starting from  
**€ 45,50**



Stem	Art.	€	Promo
Ø 3 mm	F008/3	€ 60,00	€ 45,50
Ø 6 mm	F008/6	€ 102,00	€ 81,80

**M015S**

€ 55,40

**SPIRAL POINT TAP AND DRILL SET**

With adjustable tap holder



**€ 43,70**



Taps	M3 x 0,50 mm, M4 x 0,70 mm, M5 x 0,80 mm, M6 x 1,00 mm, M8 x 1,2
Drills	Ø2,5 mm, Ø3,3 mm, Ø4,2 mm, Ø5,0 mm, Ø6,8 mm, Ø8,5 mm, Ø10

P. 060

**M312/P**

€ 60,60

**MACHINE TAP SET FOR THROUGH HOLES WITH REINFORCED SHANK**

With adjustable tap holder.



**€ 45,40**



Size	M3 x 0,50 - M4 x 0,70 - M5 x 0,80 - M6 x 1 - M8 x 1,25 - M10 x 1,50 - M12 x 1,75
------	--

Promotion valid until 31/07/2023, while stocks last - VAT not included