

S019

€ 149,00

**ENGINE STAND**

2 wheels with breaks and 2 fix wheels, possibility to tilt the motor



€ 120,00

Capacity	450 kg
Dimensions	865 x 810 x 870 mm
Net weight	21 kg

R015

€ 168,00

**CAR RAMPS SET**

2 Pcs



€ 135,00

Dimensions	905 x 330 x 218 mm
Capacity	2,5 ton
Max tire width	240 mm
Min - Max height	170 mm
Tilting	15°
Net weight	8 kg

0594

€ 147,00

**OIL DRAINER WITHOUT TANK**

With wheels, to use under lifts, for waste oil



€ 116,00

Base dimensions	390 x 390 mm
Height max	1700 mm
Net weight	13 kg

0596

€ 473,00

**PNEUMATIC OIL DRAINER**

With wheels and different size of suction probes, for waste oil, for use under lifts too



€ 379,00

Tank capacity	70 l
Measuring tank capacity	10 l
Height max	1500 mm
Metal probe	2 x ø6 mm x 695 mm
Nylon probe	2 x ø6 mm x 680 mm   2 x ø8 mm x 700 mm
Suction	ø6 x 4,5 mm - 0,4 ÷ 0,8 l/min   ø8 x 6,5 mm - 1 ÷ 1,6 l/min
Rubber hose length	Suction 1500 mm   Drain 2050 mm
Power pressure	8 ÷ 10 bar
Maximum tank pressure	0.45 bar
Net weight	25 kg

S024

€ 143,00

**ENGINE SUPPORT**

Engine support holds your engine or transmission in place during heavy automotive repairs, used to support the engine while removing gear box, transmission, replacing clutch and all motor mounts. rubber feet for safe hold of motor, easy regulation for hold engine in its place in the car. swivel and tilting holders.



€ 113,00

Capacity	500 kg
Adjusting height	205 mm
Bed length	730 ÷ 1480 mm
Net weight	13 kg

0649-

**ALUMINUM RAMPS**

In aluminum with non-slip floors. Load 170kg.



starting from  
€ 302,00

Dimensions	Capacity	Max Working angle	Max Working height	Art.	€	Promo
1520 x 735 mm	170 kg	12,5 % (7°)	180 mm	0649/1500	€ 380,00	€ 302,00
1800 x 735 mm	150 kg	12,5 % (7°)	220 mm	0649/1800	€ 472,00	€ 368,00

0595

€ 295,00

**OIL DRAINER**

With tank and wheels, to use under lifts, for waste oil



€ 233,00

Tank capacity	70 l
Height min - max	1170 ÷ 1860 mm
Maximum tank pressure	0.45 bar
Net weight	23 kg

0630/2720

€ 1050,00

**12V ELECTRIC WINCH - DIRECT CURRENT**

Permanent magnet motor, metal frame, strong cable, with anti unwinding device and cable guide. To be used only for horizontal pulling, not suitable for lifting.

SUPER PROMO

IP55



€ 495,00

Rated line pull	2720 kg
Speed	1,3 - 4,5 m / min
Motor	12 V 1,3 kW 1,8 hp
Gear Reduction ratio	294:1
Cable size	ø 7,2 mm x 32 m
Drum dimensions	ø 63 x 228 mm
Overall dimensions	520 x 180 x 175h mm
Net weight	29 kg