



| FASCO MODEL       | TYPE | DIA. | HP                    | VOLTS   | RPM       | SPD. | AMPS            | ROT. | BRNG. | SHAFT DIM.  | "A" DIM. | CROSS REF.                    | FIG. | NOTES |
|-------------------|------|------|-----------------------|---------|-----------|------|-----------------|------|-------|-------------|----------|-------------------------------|------|-------|
| <b>RHEEM/RUUD</b> |      |      |                       |         |           |      |                 |      |       |             |          |                               |      |       |
| A066              | SP   | -    | 1/30                  | 120     | 3000      | 1    | 1.27            | CW   | BALL  |             |          | 70-24157-03, 117847-00        | A    |       |
| A240              | SP   | 3.3  | 1/50                  | 115     | 3000      | 1    | 1.1             | CCW  | SLV   |             |          | 7021-8183, 70-21496-83        | B    |       |
| A241              | SP   | 3.3  | 1/25                  | 208-230 | 3200      | 1    | 0.62            | CW   | SLV   |             |          | 7021-9567, 70-23641-81        | C    |       |
| A242              | SP   | 3.3  | 1/50                  | 115     | 3400      | 1    | 1.36            | CW   | SLV   |             |          | 7021-7150, 70-22436-01        | D    |       |
| A243              | SP   | 3.3  | 1/50                  | 115     | 3400      | 1    | 1.36            | CW   | SLV   |             |          | 7021-7790, 70-22436-02        | E    |       |
| A244              | SP   | 3.3  | 1/20                  | 208-230 | 3300      | 1    | 0.85            | CCW  | BALL  |             |          | 7021-6967, 70-42241-01        | F    |       |
| A245              | SP   | 3.3  | 1/15                  | 208-230 | 3000      | 1    | .95/.85         | CW   | BALL  |             |          | 7021-7490, 70-42278-02        | G    |       |
| A246              | PSC  | 3.3  | 1/20                  | 115     | 3400/2400 | 2    | 0.85            | CW   | BALL  |             |          | 7062-3925, 70-24206-01        | H    |       |
| A247              | PSC  | 3.3  | 1/40                  | 115     | 3250/2800 | 2    | .95             | CW   | SLV   |             |          | 7062-5519                     | I    |       |
| D724              | PSC  | 5.6  | 3/4 - 1/2 - 1/3 - 1/4 | 115     | 1075      | 4    | 9.5-7.2-5.6-3.5 | REV  | SLV   | 1/2 X 6     | 5 3/4    | VARIOUS                       | J    |       |
| D806              | PSC  | 5.6  | 1/2 - 1/3 - 1/4 - 1/5 | 115     | 1075      | 4    | 7.3             | REV  | SLV   | 1/2 X 3 3/4 | 4 3/4    | 51-23012-41                   | J    |       |
| D2800             | PSC  | 5.6  | 1/2                   | 208/230 | 1075      | 1    | 2.9             | REV  | SLV   | 1/2 X 5     | 5        | K55HXMYC-4445, 51-23052-11    | K    | 36    |
| D2834             | PSC  | 5.6  | 1/3                   | 208/230 | 1075      | 1    | 2               | CW   | SLV   | 1/2 X 4 1/4 | 4        | 51-21853-83                   | L    |       |
| D2840             | PSC  | 5.6  | 1/5                   | 208/230 | 1075      | 1    | 1.3             | CW   | SLV   | 1/2 X 4 1/8 | 3 3/4    | 51-21853-82                   | L    |       |
| D2842             | PSC  | 5.6  | 1/6                   | 208/230 | 825       | 1    | 1.2             | CW   | SLV   | 1/2 X 4 1/4 | 4        | 51-20760-11                   | M    |       |
| D832              | PSC  | 5.6  | 1/8                   | 208-230 | 825       | 1    | 1.1             | REV  | SLV   | 1/2 X 4 3/4 | 4        | 21276-02, 21276-01, 512076-01 | N    |       |
| D2844             | PSC  | 5.6  | 1/10                  | 208/230 | 825       | 1    | 0.8             | CW   | SLV   | 1/2 X 4 1/4 | 3 3/4    | 51-20761-11                   | M    |       |

NOTES: 36: Has 4 drilled and tapped holes in shell



FIG. A A066



FIG. B A240



FIG. C A241



FIG. D A242



FIG. E A243



FIG. F A244



FIG. G A245



FIG. H A246



FIG. I A247



FIG. J D724, D806



FIG. K D2800




FIG. L D2834, D2840



FIG. M D2842, D2844



FIG. N D832



NEW ITEM! See page 113 for a complete listing of all our new products.

Thermally protected • UL recognized • CSA or ULc certified

NOTE: Rotation is determined by looking at shaft end. Shaft length is measured from motor face.