

PRODUCT INFORMATION PACKET



Model No: 3S048

Catalog No: 3S048

OEM Replacement Motor, 1/5 HP, 1 Ph, 60 Hz, 208-230 V, 810 RPM, 1 Speed, 48 Frame, TEAO



Regal and Genteq are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	1/5 Hp	Output KW	0.15 kW
Frequency	60 Hz	Voltage	208-230 V
Current	1.20 A	Speed	810 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	No	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Poles	8
Rotation	Clockwise	Mounting	Extended Studs
Motor Orientation	Vsd	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	7.81 in
Frame Length	3.82 in	Shaft Diameter	0.500 in
Shaft Extension	3.25 in	Thru-bolts Extension	N/R in
Outline Drawing	5KCP39FFBC51AS	Connection Drawing	NP24X327056

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022



4

3

2

1

3 of 4

REV	THIRD ANGLE PROJECTION		Uncontrolled Copy				REVISIONS	
		REV	DESCRIPTION	DATE	APPROVED			
		1 CAS 2/11/99 ELECTRONIC FORMAT						
SH	CONFIDENTIAL AND PROPRIETARY							
SIZE	DWG NO	NP 24X327056	This document is the property of General Electric Company and contains proprietary and confidential information of the Motor Business Group (MBG). The document is loaned on the express conditions that neither it nor the information contained therein shall be disclosed to others without the express consent of MBG and that the information shall be used by the recipient only as approved expressly by MBG. Also, the document shall be returned to MBG upon its request.					
NOTE: THIS DRAWING WILL BE ELECTRONICALLY REPRODUCED BY THE HVAC FAN MOTOR NAMEPLATE SYSTEM.								
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE		GE Motors		
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± ANGLES ± FRACTIONS ± MATERIAL: APPLIED PRACTICES:		DRAWN RL UETRECHT		4/3/1972		Fort Wayne, Indiana		
		CHECKED				NAMEPLATE LABEL		
		ENGRG						
		ISSUED						
		CAD NO		SIZE A		FSCM NO		
				SCALE 3		DWG NO NP 24X327056		
						SHEET 1 OF 1		
F39: XNP8				4 of 4		DISTR TO		