

0691/400V

€ 2570,00

TILTING BELT SANDER

Belt dimensions	2000 x 150 mm
Speed	(2) 18 / 37 mm/sec
Three-phase motor	400 V 50 Hz 4 kW
Net weight	110 kg

€ 2020,00

0560

€ 703,00

BENCH CHAMFERING MACHINE

Chamfer	45° 0 - 5 mm
Speed	2800 rpm
Motor	230 V 50 Hz 0,25 kW
Table dimensions	2 - 400 x 50 mm
Mill size	Ø 80 mm - Z 8
Insert	SPUN13P
Net weight	21 kg

€ 560,00

0776

€ 1160,00

ROLL FORMING MACHINE

With 3 rollers, with bench equipped with a shelf, removable central roller to create complete tubes.



Max length	1000 mm
Max thickness	0,8 mm
Roller diameter	50 mm
Net weight	105 kg

€ 961,00

0235

€ 241,00

MINI HAND ROLL FORMING MACHINE

With 3 rollers, vice not included



Max length	300 mm
Max thickness	2,5 mm
Roller diameter	30 mm
Net weight	10 kg

€ 187,00

0662

€ 706,00

TILTING BELT SANDER WITH BENCH

Bench to be assembled



Belt dimensions	1219 x 152 mm
Disc diameter	Ø 230 mm
Working table dimensions	330 x 152 mm
Belt speed	330 m/min
Disc speed	1400 m/min
Dimensions	710 x 510 x 1000 mm
Motor	230 V 50 Hz 0,75 kW
Net weight	54 kg

€ 559,00

C022/100

€ 2540,00

ROLL FORMING MACHINE

With 3 rollers, removable central roller to create complete tubes.



Max length	1000 mm
Max thickness	2 mm
Roller diameter	60 mm
Net weight	200 kg

€ 1860,00

0776/610

€ 506,00

ROLL FORMING MACHINE

3-roller, bench-top, removable central roller to create complete tubes.



Max length	610 mm
Max thickness	0,8 mm
Roller diameter	38 mm
Net weight	37 kg

€ 382,00

0775

€ 1600,00

BENDING MACHINE

Max length	1000 mm
Max. shearing thickness	1,2 mm
Max bending angle	140°
Net weight	130 kg

€ 1280,00