

PRODUCT INFORMATION PACKET



Model No: 6010
Catalog No: 6010

EVERGREEN® IM Fan and Blower Motor, 1 - 1/2 HP, 1 Ph, 60/50 Hz, 115/230 V, 1075 RPM, 1 Speed,
48 Frame, OPAO



Regal and Genteq are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1 - 1/2 Hp
Output KW	0.75 kW	Voltage	115/230 V
Speed	1075 rpm	Service Factor	1
Frame	48	Enclosure	Open Air Over
Thermal Protection	Electronically Protected	Ambient Temperature	40 °C
Frequency	60/50 Hz	Current	11.0/6.7 A
Duty	Continuous Air Over	Insulation Class	B
UL	No	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Electronically Commutated Motor	Poles	12
Rotation	Counterclockwise/Clockwise	Mounting	Round
Motor Orientation	Hor	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	12.76 in
Frame Length	6.32 in	Shaft Diameter	0.500 in
Shaft Extension	4.92 in		
Connection Drawing	NR	Outline Drawing	5SME39SXL111

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/18/2025



