

# PRODUCT INFORMATION PACKET



Model No: 6510V  
Catalog No: 6510V

EVERGREEN® VS Fan and Blower Motor, 1 HP, 1 Ph, 60 Hz, 120/240 V, 1050 RPM, 1 Speed, 48 Frame, OPAO



Regal and Genteq are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications


Phase	1	Output HP	1 Hp
Output KW	0.75 kW	Voltage	120/240 V
Speed	1050 rpm	Service Factor	1
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	12.8/7.4 A
Duty	Continuous Air Over	Insulation Class	B
UL	No	CSA	N
CE	Y	Number of Speeds	1

### Technical Specifications

Electrical Type	Electronically Commutated Motor	Poles	12
Rotation	Counterclockwise/Clockwise	Mounting	Round
Motor Orientation	Vsd	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	12.71 in
Frame Length	5.57 in	Shaft Diameter	0.500 in
Shaft Extension	5.00 in		
Outline Drawing	5SME39SXL3222	Connection Drawing	N/R

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/30/2024

CONNECTOR ID	DESCRIPTION
+V	12V INPUT
Tx	SERIAL DATA OUTPUT
Rx	SERIAL DATA INPUT
C	COMMON
JMP	JUMPER APPLICATION FOR 120VAC LINE INPUT ONLY SEE NOTE 4
	GROUND
N	AC LINE
L1	AC LINE



- NOTE - 1
- FOR VUI MOTOR (5SME39SXL3222A), USE #CPN 6510VUI
  - FOR VS MOTOR (5SME39SXL3222), USE #CPN 6510V

NAMEPLATE DATA	
MODEL	SEE NOTE - 1
CPN/STOCK NO	SEE NOTE - 1
HP	1HP
RPM	1050
VOLTS	120/240
HZ	60/50
AMPS	12.8/7.4
ROTATION	CCW/CW
MTG. POSITION	VSD

VENTILATION SYSTEM	
SHELL VENTS	OPEN
ENDSHIELD (LE)	NA
ENDSHIELD (OLE)	CLOSED

- NOTES:
1. BELLY BAND MUST BE PLACED WITHIN AREA "A" ONLY
  2. OPTIONAL EXTERNAL #8 SELF TAPPING GROUND SCREW AND TERMINAL MAY BE PROVIDED BY CUSTOMER AT LOCATION SHOWN.
  3. SUGGESTED MATING CONNECTORS:  
5 PIN CONNECTOR - TYCO 350809-1  
4 PIN CONNECTOR - TYCO 350779-1  
SOCKET (TIN) - FOR .060-.130 WIRE INS. DIA RANGE - TYCO 350536-1  
FOR .130-.200 WIRE INS. DIA RANGE - TYCO 350537-1
  4. WARNING: APPLYING 240VAC LINE INPUT WITH JUMPER APPLIED WILL PERMANENTLY DAMAGE UNIT.

DRAWING REVISION E	REVISION BY SAI KIRAN.R	REV DATE/© DATE 8/7/2023
REQUEST NUMBER ECR-0227061	APPROVED BY DON.S	DATE 8/7/2023
REQUEST NUMBER DESCRIPTION UPDATED AS PER ECR-0227061		
<small>COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.</small>		

PRIMARY DIMENSIONS ARE INCH  
mm DIMENSIONS IN [BRACKETS]  
ARE FOR REFERENCE ONLY

DRAWN BY KEP	DATE 11/20/2017
APPROVED BY ANDREA	DATE 11/20/2017
REFERENCE	
THIRD ANGLE PROJECTION	

12.71	5.00	4.50	5.57	7.71
"C"	"N"	"K"	"XA"	"AG"

		Regal Beloit America, Inc.	
DESCRIPTION		OUTLINE	
ECM EVERGREEN VUI - 1HP			
MATERIAL	PROCESS/FINISH	SIZE B	DRAWING NUMBER 5SME39SXL3222
		SHEET 1 OF 1	