

S503 €157,00

WET DRY BENCH GRINDER

With wet grinding wheel and dry grinding wheel



€121,00

Dry grinding wheel	2950 rpm - Ø 150 x 20 x 16 mm GR80
Wet grinding wheel	130 rpm - Ø 200 x 40 x 20 mm GR80

Motor	230 V 50 Hz 0,40 kW
Usage type	S2 - 10 min
Net weight	10 kg

S383 €173,00

BENCH GRINDER WITH BELT



€134,00

Dry grinding wheel	2950 rpm Ø 150 x 20 x 16 mm GR36
Belt	50 x 686 mm GR100

Motor	230 V 50 Hz 0,40 kW
Usage type	S2 - 10 min
Net weight	8 kg

0023 €100,00

BENCH GRINDER

Grinding wheel protection screens. Bracket for piece support.



€82,60

Dry grinding wheel	2950 rpm - Ø 150 x 20 x 12,7 mm GR36 - GR80
--------------------	---

Motor	2950 rpm - 230 V 50 Hz 0,35 kW
Usage type	S2 - 10 min
Net weight	7 kg

0555 €127,00

GRINDING WHEEL STAND



€97,80

Height	760 mm
Column	Ø 75 mm
Table dimensions	320 x 210 mm
Net weight	13,5 kg

S023 €137,00

BENCH GRINDER

With two grinding wheels of different grain



€108,00

Dry grinding wheel	2950 rpm - Ø 150 x 20 x 16 mm GR36 - GR80
Motor	2950 rpm - 230 V 50 Hz 0,40 kW

Usage type	S2 - 10 min
Net weight	8 kg

0510 €111,00

BENCH GRINDER WITH BRUSH

With grinding wheel and brush. Bracket for supporting pieces. Holes for fixing on the bench.



€90,30

Brush	2950 rpm - Ø 150 x 20 x 12,7 mm
Dry grinding wheel	2950 rpm - Ø 150 x 20 x 12,7 mm GR36

Motor	230 V 50 Hz 0,35 kW
Usage type	S2 - 10 min
Net weight	7 kg

0503 €114,00

WET DRY BENCH GRINDER

With water grinding wheel and dry grinding wheel.



€93,20

Dry grinding wheel	2950 rpm - Ø 150 x 20 x 12,7 mm GR80
Wet grinding wheel	130 rpm - Ø 200 x 40 x 20 mm GR80

Motor	230 V 50 Hz 0,35 kW
Usage type	S2 - 10 min
Net weight	9 kg

0106 €97,80

GRINDING WHEEL STAND

Light duty.



€76,70

Height	760 mm
Column	Ø 75 mm
Table dimensions	320 x 210 mm
Net weight	11 kg