



# Switch-Pro™ Remote Level Controllers

## Overview

CSA approved, the Switch-Pro general purpose level controllers are offered in three configurations for alarms, pump and valve control. The LC40 accepts one level sensor input and provides one 10A relay for high level or low level alarm. The LC41 accepts two level sensor inputs and provides one latching 10A relay for automatic fill or empty control. The LC42 accepts three level sensor inputs with one latching 10A relay output for automatic fill or empty control, and a second non-latching 10A relay for high level or low level alarm.

Part No. [LC40-1001](#)Part No. [LC41-1001](#)Part No. [LC42-1001](#)

## Features

- Fail-safe relay control of pumps or valves with 0-60 second delay
- Easy setup with LED indicators for sensor, power and relay status
- 35mm DIN rail mount or panel mount polypropylene (PP) enclosure with removable terminal strips
- Invert switch changes relay state from NO to NC without rewiring
- Mounts easily in control panel
- Connects to any Flowline level switch
- Interfaces directly with any horn, buzzer, valve, etc...
- Use LC41, LC42 version for automatic fill/empty operations
- Made in the USA
- 2-year warranty



## Switch-Pro LC Series Technical Specifications

| Model               | <a href="#">LC40-1001</a>                              | <a href="#">LC41-1001</a>   | <a href="#">LC42-1001</a>                         |
|---------------------|--------------------------------------------------------|-----------------------------|---------------------------------------------------|
| Price               | \$275.00                                               | \$325.00                    | \$385.00                                          |
| Weight (lb)         | 1.9                                                    | 1.9                         | 1.9                                               |
| Supply Voltage      | 120VAC @ 50-60 Hz (can be field configured for 240VAC) |                             |                                                   |
| Consumption         | 5W maximum                                             |                             |                                                   |
| Sensor Inputs       | (1) two wire level switch                              | (2) two wire level switches | (3) two wire level switches                       |
| Sensor Supply       | 13.5 VDC @ 27mA                                        |                             |                                                   |
| LED Indication      | Sensor (green), power (green) & relay (red)            |                             |                                                   |
| Contact Type        | (1) SPDT relay (non-latching)                          | (1) SPDT relay (latching)   | (2) SPDT relays, (one non-latching, one latching) |
| Contact Rating      | 250VAC @ 10A                                           |                             |                                                   |
| Contact Output      | Selectable NO / NC                                     |                             |                                                   |
| Contact Latch       | N/A                                                    | Selectable ON / OFF         | Selectable ON / OFF                               |
| Contact Delay       | 0-60 seconds                                           |                             |                                                   |
| Ambient Temperature | -40°F to 158°F [-40°C to 70°C]                         |                             |                                                   |
| Enclosure Mounting  | 35mm DIN rail or thru-hole panel mount                 |                             |                                                   |
| Enclosure Material  | PP (polypropylene), UL94VO                             |                             |                                                   |
| Classification      | General purpose                                        |                             |                                                   |
| Compliance*         | CSA LR 79326                                           |                             |                                                   |

\* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at [www.AutomationDirect.com](http://www.AutomationDirect.com)



# Switch-Pro™ Remote Level Controllers

## Wiring

**LC40 series:** 1 sensor input, 1 relay output.

**Typical Application:**

High level or low level alarm



**LC41 series:** 2 sensor inputs, 1 relay output. The relay included is a latching relay.

**Typical Application:**

Automatic fill or empty




**LC42 series:** 3 sensor input, 2 relay outputs. One relay is latching and the other is a single input relay.

**Typical Application:**


Automatic fill or empty with high level or low level alarm




**Low Level Alarm Output Wiring Example (One level sensor input required):**




**Automatic Fill Output Wiring Example (Two level sensor inputs required):**



**High Level Alarm Output Wiring Example (One level sensor input required):**




**Automatic Empty Output Wiring Example (Two level sensor inputs required):**



**Symbol Key:**



**Level Sensor Input Wiring Example:**





LV10 series can be wired using the White and Black wires for NO operations or the Red and Black wires for NC operations.

## Dimensions

inches [mm]

MODEL LC42



See our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete Engineering drawings.

## Compatible Products

### ProSense Float Level Switches



### Switch-Tek™ Level Switch Sensors

