


# ADD TO C-RAIL FESTOON KITS SHOWN ON PRECEDING PAGES


## COMPONENTS - C-Rail Festoon

### For FLAT Cable




**FLAT CABLE END CLAMP**

Model No.	A in. (mm)	B in. (mm)	C in. (mm)	Wt. lbs. (Kg)
C35-FE-02	2.00 (51)	1.00 (25)	1.50 (38)	1.46 (.66)
C35-FE-03	3.12 (80)	1.56 (40)	0.94 (24)	1.63 (.73)



**FLAT CABLE INTERMEDIATE TROLLEYS**


Model No.	A in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	Wt. lbs. (Kg)
C35-FC-32	2.00 (51)	0.56 (14)	3.12 (79)	3.72(94)	0.84 (.38)
C35-FC-52	2.00 (51)	1.50 (38)	5.00(127)	4.76(121)	0.94 (.42)
C35-FC-53	3.12 (80)	0.94 (24)	5.00(127)	4.31(109)	1.11 (.50)



**FLAT CABLE TOW TROLLEY**


Model No.	A in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	Wt. lbs. (Kg)
C35-FT-52	2.00 (51)	1.50 (38)	5.00(127)	8.18(208)	2.38(1.07)
C35-FT-53	3.12 (80)	0.94 (24)	5.00(127)	8.18(208)	2.45(1.10)

### For ROUND Cable or Hose




**ROUND CABLE/HOSE END CLAMP**

Model No.	A in. (mm)	B in. (mm)	C in. (mm)	Wt. lbs. (Kg)
C35-RE-11	0.31-0.59 (8-15)	1.10 (28)	2.75 (70)	1.41 (.63)
C35-RE-12	0.60-0.94 (15-24)	1.25 (32)	3.86 (98)	1.53 (.69)
C35-RE-13	0.95-1.25 (24-32)	1.47 (37)	5.59(142)	1.85 (.83)



**ROUND CABLE/HOSE INTERMEDIATE TROLLEY**


Model No.	A in. (mm)	B in. (mm)	C in. (mm)	Wt. lbs. (Kg)
C35-RC-11	0.31-0.59 (8-15)	1.10 (28)	2.75 (70)	1.41 (.63)
C35-RC-12	0.60-0.94 (15-24)	1.25 (32)	3.86 (98)	1.53 (.69)
C35-RC-13	0.95-1.25 (24-32)	1.47 (37)	5.59(142)	1.85 (.83)



**ROUND CABLE/HOSE TOW TROLLEY**


Model No.	A in. (mm)	B in. (mm)	C in. (mm)	Wt. lbs. (Kg)
C35-RT-11	0.31-0.59 (8-15)	6.50 (165)	2.75 (70)	2.33(1.05)
C35-RT-12	0.60-0.94 (15-24)	6.70 (170)	3.86 (98)	2.45(1.10)
C35-RT-13	0.95-1.25 (24-32)	6.92 (176)	5.59(142)	2.77(1.25)

## ACCESSORIES




**C-RAIL TRACK-GALVANIZED**


Model No.	A ft. (m)	Wt. lbs. (Kg)
C35-TR-06	6 (1.8)	6.3 (2.84)
C35-TR-12	12 (3.6)	12.6 (5.67)
C35-TR-18	18 (5.4)	18.9 (8.51)




**END STOP WS30-ES**  
Wt. = 0.3 lbs




**TRACK COUPLER C35-CP-01**  
Weight = 1.0 lbs



**COUPLER/HANGER BRACKET C35-CP-02**  
Wt. = 1.25 lbs




**TRACK HANGER C35-HB-03**  
Wt. = .55 lbs




**CONTROL UNIT ASSEMBLY WITH 2 TROLLEYS**

Model No.	Wt. lbs. (Kg)
C35-UN-01	4.00 (1.8)
C35-UN-02	8.00 (3.6)

Order End Clamp and Glands separately.



**VERTICAL MOUNT HANGER C35-HB-02**  
Wt. = 1.25 lbs




**HORIZONTAL MOUNT HANGER C35-HB-01**  
Wt. = 1.25 lbs



**BEAM CLAMP C35-BCA**  
Wt. = 0.34 lbs

### TOW ARM

Attaches to your machine and inserts into Tow Trolley to tow the system.



DESCRIPTION	WGT lb. (kg)	MODEL NUMBER
TOW ARM	1.3 (59)	CTA-01

### FLAT-TO-ROUND CABLE CONNECTOR SET



Go quickly and safely from flat to round cable. Consists of one each male and female plugs designed to accept flat or round cable and lock together securely. Plugs are 3-pole, 4-wire plus ground and will accommodate round cable sizes #14 AWG through #10 AWG; flat cable up to 1.00" wide. Ratings: 20 amp, 480 volt, 3 phase. NEMA configuration #L16-20. Plugs are double-insulated plastic and resist impact, corrosion and most chemicals.

DESCRIPTION	MODEL NUMBER
Set of 2 Locking Plugs	LC-01