

PRODUCT INFORMATION PACKET



Model No: 5SME39HXL175I-P
Catalog No: 5SME39HXL175I-P
REY BUILT - MTR FROM INDIA

Regal and Genteq are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/2 Hp
Voltage	208-230/277 V	Speed	1050 rpm
Service Factor	1	Frame	48
Enclosure	Open Air Over	Thermal Protection	No Protection
Ambient Temperature	40 °C	Frequency	60/50 Hz
Current	3.6 A	Duty	Continuous Air Over
Insulation Class	B	UL	Recognized
CSA	N	CE	N
Number of Speeds	1		

Technical Specifications

Electrical Type	Electronically Commutated Motor	Poles	12
Rotation	Counterclockwise/Clockwise	Mounting	Round
Motor Orientation	Vsd	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	9.67 in
Frame Length	4.82 in	Shaft Diameter	0.500 in
Shaft Extension	3.92 in		
Outline Drawing	5SME39HXL175I	Connection Drawing	24X328008

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/19/2025


Winding and Test Specification

WTS # 24X332717-1																	
Revision # 2				Rev. Date : Jul 13, 2018				First Made for :									
WTS Nameplate Data																	
Horsepower	1/2		RPM	1050													
Voltage	277/208-230/115		Amps	4.10 6.80													
Frequency	60/50		Phases	1													
Capacitor			Cap Volts														
Test Volts : 115				Low Spd St Volts :													
Test Frequency : 60																	
Test Instructions : 24A105040AA-P1																	
Winding		Resistance															
		Min	Nominal		Max												
Main *	6.17	6.50		6.83													
X Main	6.17	6.50		6.83													
Y Main																	
Z Main																	
W Main																	
Start	6.17	6.50		6.83													
N. L. Performance Data																	
	Amps		Watts		Cap. Volts							Full Load Performance		Speed		Torque	
	Nominal	Nominal	Max	Nominal		Max	Nominal	Max	Nominal	Min	Nominal						
High	3.55	33	40														
Med. High																	
Medium																	
Med. Low																	
Low																	
Max. Torque																	
	RPM	Torque		Locked Rotor													
		Min	Nominal	Amps	Watts	Torque	Nominal	Nominal									
High				Nominal													
Med. High																	
Medium																	
Med. Low																	
Low																	
Customer/Special Load Points																	
	Speed	Torque		Watts		Amps											
	Nominal	Min	Nominal	Nominal	Max	Nominal	Max										
High																	
Med. High																	
Medium																	
Med. Low																	
Low																	


* Large wire size may be double stranded.

NAME: 501108895 OBJECT: 24X328008 DATE: 16-May-05 19:37:32

REV	SHEET	DRAWING NO.	SIZE	REVISIONS			
				REV.	DESCRIPTION	DATE	APPROVED
2	24X328008	A	A	1	MODIFIED PER ISAAC 05-1148	SURAJ 05/16/05	PALESH
				2	CHANGED "GE" FORMAT TO "RBC" FORMAT AS PER ISAAC 05-1777	GEETHA 09/05/05	PALESH

RBC PROPRIETARY AND CONFIDENTIAL INFORMATION	
This document is the property of REGAL-BELOIT CORPORATION ("RBC") including its subsidiaries and divisions and contains proprietary information of RBC. This document is loaned on the express condition that neither it nor the information contained therein shall be disclosed to others without the express written consent of RBC, and that the information shall be used by the recipient only as approved expressly by RBC. This document shall be returned to RBC upon its request. This document may be subject to certain restrictions under U.S. export control laws and regulations.	
THIRD ANGLE PROJECTION	
	

230V UNIT CONNECTION



FOR ADDITIONAL INFO REFER TO:	SIGNATURES	DATE
APPLIED PRACTICES	MODEL	
DIMENSIONS ARE IN INCHES	DETAIL	SREYAS 05/09/05
TOLERANCE ON:	CHECKED	
1 PL DECIMALS ± 0.1	ENGRG	
2 PL DECIMALS ± 0.01	MFG	
3 PL DECIMALS ± 0.005	QUALITY	
ANGLES ± 0.5	ISSUED	
FRACTIONS ±		
FINISH		

TITLE	
NAME PLATE CONNECTION DIAGRAM	
FMF X-13 MODELS	

SIZE	DRAWING	REV
A	24X328008	2

SCALE:		SHEET
		1 of 1

Winding and Test Specification

WTS # 24X332717-1													
Revision # 2				Rev. Date : Jul 13, 2018				First Made for :					
WTS Nameplate Data													
Horsepower	1/2		RPM									1050	
Voltage	277/208-230/115		Amps									4.10 6.80	
Frequency	60/50		Phases									1	
Capacitor			Cap Volts										
Test Volts : 115		Low Spd St Volts :											
Test Frequency : 60													
Test Instructions : 24A105040AA-P1													
Winding		Resistance											
		Min	Nominal									Max	
Main *	6.17	6.50	6.83										
X Main	6.17	6.50	6.83										
Y Main													
Z Main													
W Main													
Start	6.17	6.50	6.83										
	N. L. Performance Data				Full Load Performance								
	Amps	Watts		Cap. Volts	Amps		Watts		Speed	Torque			
	Nominal	Nominal	Max		Nominal	Max	Nominal	Max	Nominal	Min	Nominal		
High	3.55	33	40										
Med. High													
Medium													
Med. Low													
Low													
	Max. Torque			Locked Rotor									
	RPM	Torque		Amps	Watts	Torque	Nominal	Nominal					
		Min	Nominal										
High				Nominal									
Med. High													
Medium													
Med. Low													
Low													
	Customer/Special Load Points												
	Speed	Torque		Watts		Amps							
	Nominal	Min	Nominal	Nominal	Max	Nominal	Max						
High													
Med. High													
Medium													
Med. Low													
Low													

* Large wire size may be double stranded.



Motor Details

Model :	5SME39HXL175I	Catalog Number :	N/A
General:			
Application :	INDOOR INT CONTROL	Motor Category :	COMPLETE MOTOR
Phases :	1	Production Status :	PROD
# of Speeds :	1	Stock Status :	
Testspec :	24X332717-1	Approved For Sale :	
Horiz/Vertical :	VSD	Restricted Model :	
Shell Enclosure :	OPEN	Customer :	ALL
Endshield Enclosure :	CLOSED	Customer Part# :	N/R
Nameplate Data:			
Horsepower :	1/2	GE Type :	SME
RPM :	1050	Time Rating :	CAO
Voltage :	208-230/277	Frequency :	60/50
FL Amps :	3.6	Insulation Class:	B
Capacitor 1mFd/V :	N/R	Capacitor 2mFd/V :	N/R
Additional Information :	N/R		
Miscellaneous:			
Fullload RPM - HI :		GE Frame :	39
Poles :	12	Shell Length :	4.82
Rotation :	CCW/CW	Drains :	Y
Thermal Protection :		Est. Weight :	12
Finish Color:	STD GRAY	Capacitor By :	N/R
OVERLOAD INFORMATION::			
Protector:	N/R	Overload Temp :	N/A
Catalog No:	N/A	Vendor Name:	N/A
THERMAL CUT-OFF INFORMATION:			
TCO:	N/A	Overload Temp :	N/A
Catalog No:	N/A	Vendor Name:	N/A
U.L.CONSTRUCTION FILES:			
Motor Construction:	E46035(excluding SME)	Class B Insulation :	E306343(excluding SME)
Over Load :	E27885(excluding SME)	CSA(REY) :	MC236833(excluding SME)
Shaft:			
PE Type :	FLAT	OPE Type :	N/R
PE Length :	3.92	OPE Length :	N/R
PE Diameter :		OPE Diameter :	
PE Flat Length :	3.50	OPE Flat Length :	N/R
Endshields:			
PE Material :	AL	OPE Material :	AL
PE Hub Type :	FLAT	OPE Hub Type :	FLAT
PE Oiler :	N/R	OPE Oiler :	N/R
PE Oil Plug :	N/R	OPE Oil Plug :	N/R
PE Mounting Holes :	N/R	OPE Mounting Holes :	N/R
Bearings:			
PE Bearing Type :	BALL	OPE Bearing Type :	BALL
Bearing Protection :	No	Rohs Compliant :	No
Mounting:			
Base :	N/R	Lug :	N/R
Clamp Screw :	Yes	Weld Screw :	No
Extended Clamp Screws:			
PE Pattern :		OPE Pattern :	
PE Length :	0	OPE Length :	0
PE Nut Qty :	0	OPE Nut Qty :	0
Head End :	PE	Screw Size :	#8
Nut Thickness :	.12		
Lead & Cord :			
Lead End :	OPE	Lead Type :	SINGLE COND
Lead Exit H/W :	N/R	Lead Harness Desc :	LEAD HARNESS
Lead Exit H/W Orient. :	N/R		
Note : Exit position is viewed from the Lead End with the Shell Weld at 6:00.			
Grounding :			
Type :	N/R	Location :	N/R viewed from N/R with Oil boss at 12:00
Exit Type :	N/R	AWG Size :	0
Length :	N/R	Color :	N/R
Terminal :	N/R	Ins.Material & Thickness	N/R N/R
Diagrams and Dimensions :			
Outline Drawing :		C-Dimension :	
Connection Diagram :	423B631 Fig# 35	Connection Label :	24X328008
Notes :			
This document is the property of the Regal Beloit Company containing proprietary and confidential information			

