

Tang break-off tools for **HELICOIL® Plus** and **HELICOIL® Classic**



From sizes M 14, the tang can be broken off with long-nosed pliers.

Thread size	Tang break-off tool für HELICOIL® Plus	
d x P	Order no.	€
M 2	0158 040 0000	on request
M 2.5	0158 040 1000	on request
M 3	0158 040 1000	on request
M 3.5	0158 040 2000	on request
M 4	0158 040 2000	on request
M 5	0158 040 3000	on request
M 6	0158 040 3000	on request
M 6*	0185 050 3000	on request
M 7	0158 040 4000	on request
M 8	0158 040 4000	on request
M 8 x 1	0158 040 4000	on request
M 9	0158 040 4000	on request
M 10	0158 040 5000	on request
M 10 x 1	0158 040 5000	on request
M 10 x 1.25	0158 040 5000	on request
M 11	0158 040 5000	on request
M 12	0158 040 6000	on request

*M 6: for injector screw kit 4185 906 0004

Spare parts for HELICOIL® Kits – Special car solutions

For HELICOIL® Kits	Spare part	Order no.	€
Lambda probe thread M 18 x 1.5 x 9	Tool adapter 3/8"	0100 977 6001	on request
Oil drain thread M 12 x 1.5 – M 16 x 1.5	Hexagon wrench	91110.9SW2,5	on request
Oil drain thread M 12 x 1.5 – M 16 x 1.5	Calliper	4108 900 0019	on request
Wheel screw thread M 14 x 1.5 x 9	Pliers	0185 900 0001	on request
Wheel screw thread M 14 x 1.5 x 9	Screw M 10 x 35	91212.91035	on request
	Stamp	0181 914 4001	on request
	Threaded sleeve	0181 914 4002	on request
	Washer 10.5 mm	9021A10,5	on request
	Screw M 8 x 35	91212.9835	on request
Wheel screw thread M 12 x 1.5 x 12	Stamp	0181 912 4001	on request
	Threaded sleeve	0181 912 4002	on request
	Washer 8.4 mm	9021A8,4	on request
	Washer 13 mm	9021A13	on request

Tool holders with ratchet, in steel design



Clamping range	Tool length	Order no.	€
2.0 – 5.0 mm	85 mm	0149 999 0001	on request
4.6 – 8.0 mm	110 mm	0149 999 0002	on request