



## SPECIFICATIONS

<b>TEMPERATURES:</b>	
Operating Temperature (FM/ATEX Approved Flow Meters):	0°F to +129°F (-18°C to +54°C)
Operating Temperature (Non-Approved Flow Meters):	0°F to +140°F (-18°C to +60°C)
Storage Temperature:	-40°F to +158°F (-40°C to +70°C)
Standard Factory Configuration:	2 Totals (1 Resettable, 1 Cumulative); Factory Calibration in gallons or litres; User Calibration and Rate of Flow Indication
Display Electronics:	Q9 Electronics can be used on G2, TM, A1, and QSE Series Meters
Totalizing Registers:	Cumulative and Batch
K-Factor Limits:	Min: 0.001 pulses/unit; Max: 999,999 pulses/unit
Readout Totals:	LCD with floating decimal: Minimum Display = 0.001 units; Maximum Display = 999,999 x 100 units (6 digits)
Input Pulse Rate:	Frequency Range is 0.25 Hz - 3 kHz
Internal Power Supply:	2 Alkaline AAA batteries at 1.5 volts each
Alkaline Battery Life:	Typically 2 Years
Field Calibration:	Field calibrate by user methods: <ul style="list-style-type: none"> <li>• K-factor entry</li> <li>• Correction Factor (% Adjust)</li> <li>• Dispense Display</li> </ul>

## APPROVALS\*\* / WARRANTY



Select A1 & G2 models\*



\*See A1 & G2 Datasheets for models that qualify for approvals.  
\*\*All Q9 Rate / Totalizer have the CE approval.

The **FLOMEC® Q9 Rate / Totalizer** is the latest version of the popular FLOMEC® computer displays. It incorporates many of the most requested features over the years including low battery indication and the ability to display custom units with a name label. Optional plug-in daughterboard for 4-20mA, scaled pulse, and external power supply are easily added as original equipment or as a retrofit in the field. All of the daughterboard parameters are addressable through the two buttons on the Q9 display. An additional new feature is the ability to display velocity as well as rate and totals. Packaged in the same form as the familiar FLOMEC® display, the Q9 operates on two AAA batteries with approximately 2 years of operation and maintains all of the same intrinsically safe approvals of past products.

## FEATURES / BENEFITS

- Highly Visible LCD characters against a yellow-tinted background
- Many Field Configurable options for ease of operation including diagnostic mode and custom unit name
- Easily retrofit to most existing FLOMEC® turbines
- Maximum versatility with optional pre-configured plug-in daughterboard to supply 4-20mA and Scaled Pulse
- Convenient Battery Power Level indication with automatic low battery warning
- Safety first design with FM Class 1, Div 1; ATEX; IECEx; cFM; CE approvals on select A1 and G2 models
- Providing operator consistency for all of your flow meters, the Q9 can be used with G2, TM, and A1 Series Flow Meters
- Ultimate ease of operation with permanent preprogrammed 5 point factory calibration
- Accommodates a wide range of technical expertise with 3 Field calibration methods (K-Factor, Correction Factor or Dispense Display)
- For simple Plug and Play installation, the Q9 is factory calibrated set to display Cumulative Total, Re-Settable Batch Total and Rate

## USER CONFIGURATION

- PIN Protected, four-digit user selectable
- 11 preprogrammed engineering units and one user-configurable custom unit
- Alphanumeric information line for on-screen instructions and custom unit name
- Four preprogrammed, user-selectable time bases (Day, Hour, Min., Sec.)
- Configurable screen update frequency
- A user-selectable low-frequency filter
- Field Calibration is retained when switched to Factory Cal so you can have two accessible calibrations available
- Three field calibration methods available (1 point Dispense Display, 5 point Correction Factor, 5 point K-Factor)
- Diagnostic mode shows % battery life remaining

# Q9 RATE / TOTALIZER

## OTHER ELECTRONICS OPTIONS†

**42** = 4-20mA Module installed between the local display and the flow meter body

- Provides a 4-20mA signal
- Provides a Scaled NPN Open Collector Pulse
- Can provide External Power to the local display
- Comes with 10 feet of installed cable

**PO** = Pulse Output Module installed in place of the display (blind flow meter)

- Provides an Unscaled NPN Open Collector Pulse

**R9** = Replacement Q9 Computer Display for a flow meter body that has an old 09 display<sup>1</sup>

- Comes with the extra parts required to retrofit a Q9 display in place of an 09 display

<sup>†</sup>Separate data sheets available.

<sup>1</sup>FM/ATEX Approved when replacing a FM/ATEX Approved 09 display on a FM/ATEX Approved A1 or G2 flow meter.

## DIMENSIONS

Dimension "A"	Dimension "B"	Dimension "C"
3.4 in. (8.6 cm)	2.1 in. (5.4 cm)	0.85 in. (2.2 cm)

