

## MR-Conditional Line/ Model: MR7K-MAN

Seven Drawer Anesthesia Cart, Key Lock, Specialty Package



### Over 20 Drawer Colors Available:

**Antimicrobial Finish Available: Lemon Drop Yellow Only**  
BBurgundy, Red, Yellow, Beige, Sand, HammerTone Green, Teal, HammerTone Blue, Navy, Light Blue, HammerTone Gray, Light Gray, Mauve, Cream, Taupe, White, Brushed Silver, Forest Green, HammerTone Black, HammerTone Red and Pink.

### Warranty:

- 12-Year Manufacturer's Warranty on shipments to US and Canada, 5-Year Manufacturer's Warranty on all other International shipments.
- 1-Year Limited Warranty on any bought-out parts

### Construction:

- Non-magnetic or "weekly magnetic" materials including aluminum, stainless steel, plastic, and aluminum and brass attachment hardware

### Features:

- Designed for compatibility in MRI suites
- Tested by independent testing authority to Tesla 3 level (copies of report available)
- Meets American Society for testing and materials (ASTM) international, designation: F2503-5 definition of "MR-Conditional"
- Cabinet painted gloss white with MRI identification sticker applied
- Low-ferrous, ball-bearing, full extension drawer slides
- Low-ferrous 5" sealed ball-bearing casters; full swivel – one with brake, one directional
- BEST® brand lock on cabinet, with two keys
- Corner bumpers, protecting the cart
- Painted aluminum pull-out shelf
- Antimicrobial plastic top, removable
- MR-Conditional accessories available
- Latex free
- Durable, hard-baked powder coat finish

### Anesthesia Specialty Package Includes MRI-Compatible Accessories:

- Aluminum 3-tier raised back rail system (MR-RBR3)
- Aluminum side rails (4 ea.) (MR-SR)
- Plastic full drawer tray organizer (2 ea.) (68530-P1)

### Drawer Configuration:

- (1) - 4" (10.2 cm)
- (4) - 3" (8.3 cm)
- (1) - 6" (16.5 cm)
- (1) - 9" (24.8 cm)

### Internal Drawer Configuration:

- 23.9" W x 17" D (60.8 cm x 43.2 cm)

### Overall Cart Dimensions:

- 68.2" H x 32" W x 24" D (173.4 cm H x 81.3 cm W x 61 cm D)
- Cart net weight: 127 pounds (57.6 kg)
- Approximate shipping weight: 166 pounds (75.3 kg)
- Approximate shipping dims: 55" H x 37" W x 26" D (139.7 cm H x 94 cm W x 66 cm D)