



HOBO[®] U20L-01 Data Logger

Water Level (30 ft)

The HOBO U20L-01 is a low-cost, research-grade water level data logger for continuously measuring water level and temperature in a wide range of underwater environments. It features 0.1% measurement accuracy, a polypropylene housing for use in both fresh and salt water, and a non-vented design for convenient and hassle-free deployment.

This data logger requires either the U-DTW-1 Waterproof Shuttle or the Base-U-4 Base Station for configuration and data offload, HOBOWare software (free download). NOTE: HOBOWare Pro is required when using the U-DTW-1 Waterproof Shuttle. See compatible items below.

Helpful Links:

[Barometric Pressure Compensation Assistant Demo](#)

[Multi-rate Sampling Demo](#)

Key Advantages:

- Self-contained non-vented design enables easy deployment
- Ideal for use in both fresh and saltwater environments, including wells, streams, lakes, wetlands, and tidal areas
- Depths up to 30 feet
- Durable ceramic pressure sensor withstands freezing
- HOBOWare Pro software provides easy conversion to accurate water level reading, fully compensated for barometric pressure (see demo), temperature, and water density

Note: A calibration certificate is not offered for this logger. If you require a NIST-traceable calibration certificate, please see the [U20-001-01](#) (freshwater) or [U20-001-01-Ti](#) (saltwater).

Pressure (Absolute) and Water Level Measurements U20L-01

Operation Range 0 to 207 kPa (0 to 30 psia); approximately 0 to 9 m (0 to 30 ft) of water depth at sea level, or 0 to 12 m (0 to 40 ft) of water at 3,000 m (10,000 ft) of altitude

Factory Calibrated Range 69 to 207 kPa (10 to 30 psia), 0° to 40°C (32° to 104°F)

Burst Pressure 310 kPa (45 psia) or 18 m (60 ft) depth

Water Level Accuracy* Typical error: ±0.1% FS, 1.0 cm (0.03 ft) water
Maximum error: ±0.2% FS, 2.0 cm (0.06 ft) water

Raw Pressure Accuracy** ±0.3% FS, 0.62 kPa (0.09 psi) maximum error

Resolution <0.02 kPa (0.003 psi), 0.21 cm (0.007 ft) water

Pressure Response Time (90%)*** <1 second at a stable temperature; measurement accuracy also depends on temperature response time

Temperature Measurements

Operation Range -20° to 50°C (-4° to 122°F)

Accuracy ±0.44°C from 0° to 50°C (±0.79°F from 32° to 122°F), see Plot A in manual

Resolution 0.10°C at 25°C (0.18°F at 77°F), see Plot A in manual

Response Time (90%) 10 minutes in water (typical)

Stability (Drift) 0.1°C (0.18°F) per year

Logger

Real-time Clock ±1 minute per month 0° to 50°C (32° to 122°F)

Battery 2/3 AA, 3.6 Volt lithium, factory-replaceable

Battery Life (Typical Use) 5 years with 1 minute or greater logging interval

Memory (Non-volatile) 64K bytes memory (approx. 21,700 pressure and temperature samples)

Weight Approximately 154 g (5.43 oz) in air Approximately 53.9 g (1.9 oz) in fresh water

Dimensions 3.18 cm (1.25 inches) diameter, 15.24 cm (6.0 inches) length; mounting hole 6.3 mm (0.25 inches) diameter

Wetted Materials Polypropylene housing and lanyard; Viton and Buna-N O-rings; ceramic sensor in acetyl end cap; stainless steel screws suitable for saltwater

Logging Interval Fixed-rate or multiple logging intervals, with up to 8 user-defined logging intervals and durations; logging intervals from 1 second to 18 hours. Refer to the *HOBOware User's Guide* for details.

Launch Modes Immediate start and delayed start

Offload Modes Offload while logging; stop and offload

Battery Indication Battery voltage can be viewed in status screen and optionally logged in datafile. Low battery indication in datafile.

Environmental Rating: IP68

CE The CE Marking identifies this product as complying with all relevant directives in the European Union (EU).

* Water Level Accuracy: With accurate reference water level measurement, known water density, accurate Barometric Compensation Assistant data, and a stable temperature environment.

** Raw Pressure Accuracy: Absolute pressure sensor accuracy includes all sensor drift, temperature, and hysteresis-induced errors.

*** Changes in Temperature: Allow 20 minutes in water to achieve full temperature compensation of the pressure sensor. Maximum error due to rapid thermal changes is approximately 0.5%.