

Fiberglass Free-Stand Type 4X, 72x25x24.5, 3-Pt Latch, Fiberglass

CATALOG NUMBER

A722525FGFS3PT



An economical housing for corrosive environments, single-door, free-stand enclosures provide a versatile solution for applications that require flexibility when mounting panels and racks. Benefits include easy access to equipment, larger capacity for control systems, steel reinforcements for stability and strength, captivated door screws and an optional PowerGlide Handle for secure latching.

INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12; File No. E61997

Enclosure flammability evaluated per UL 508A

NEMA Type 3, 3R, 4, 4X, 12, 13

E.I.A. RS-310-D

IEC 60529, IP66

Meets NEMA Type 3RX requirements

CERTIFICATIONS



FEATURES

Fiberglass-reinforced polyester material has excellent temperature and chemical resistance and exhibits outstanding physical properties

Fiberglass material is easily punched, drilled, filed or sawed

Models have either a 3-point latching system with handle or stainless steel captivated door screws

Seamless foam-in-place gasket assures water-tight and dust-tight seal

Painted steel top, bottom and side internal reinforcements standard; stainless steel corner reinforcements optional

Heavy-duty Type 316 stainless steel lifting eyes

Accessory mounting channels attached horizontally to interior body sides at top, bottom and center; painted mounting channels standard; stainless steel optional

Panels and rack-mounting angles can be mounted anywhere along corner channels; panels can be mounted on sides or back

Hinges are corrosion-resistant fiberglass with Type 316 stainless steel hinge pins

Large, high-impact thermoplastic data pocket (12.00 x 12.00 in. or 305 x 305 mm) is

Molded-in angular sealing flange directs water away from gasket area

Type 316 stainless steel PowerGlide Handle on handle versions

Material is halogen free

Optional mild-steel panels are painted white

Optional conductive panels are unpainted

PRODUCT ATTRIBUTES

Article Number: 46889

Height: 72in

Width: 25in

Depth: 24.5in

Material: Fiberglass

Finish: Smooth Gloss

Color: Gray

Thickness: 0.22in

Weight: 215lb

ADDITIONAL PRODUCT DETAILS

For CALIFORNIA residents only - WARNING: This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm. Please note that by posting this Proposition 65 warning, we are notifying you that one or more of the Proposition 65 listed chemicals may be present in this product. With HOFFMAN's products, the exposure to these chemicals may be of no significant risk to you, but out of caution and to ensure your well-being, we have elected to place this warning on our site to make sure our customers are informed. You can find more information at <http://www.oehha.ca.gov/proposition-65/about-proposition-65>.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE