

We connect and protect

# Hol-Sealers Hole Seal, 4.12-inch Diameter, Gray, Mild Steel

## Catalog Number

AS300

HoleSeals Product Photo

- Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals . Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.

## Industry Standards

- UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)
- UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)
- Steel Hole Seals
- CSA File No. 42186; Type 3R, 4, 12, 13
- NEMA/EEMAC Type 3R, 4, 12, 13
- IEC 60529, IP66
- Stainless Steel Hole Seals
- CSA File No. 42186; Type 3R, 4, 4X, 12, 13
- NEMA/EEMAC Type 3R, 4, 4X, 12, 13
- IEC 60529, IP66

## Features

- Available in multiple colors and sizes
- Oil-resistant gasket provided
- Steel model has plated stud (10-32x5/8) and wing nut
- Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

## PRODUCT ATTRIBUTES

- Article Number: 59780
- Material: Mild Steel
- Finish: Powder Coated
- Color: Gray
- Color Code: ANSI 61
- Thickness: 16ga
- Hole Diameter: 3.62in max
- Hol-Sealer Diameter: 4.12in
- Weight: 0.57lb

## Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



# nvent

Our powerful portfolio of brands:

- Caddy
- Erico

- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/HOFFMAN](https://nVent.com/HOFFMAN) |