

# CT Mounting Base 1-Phase Mechanical Lugs and Studs, 400 Amp, Unpainted, Steel

## CATALOG NUMBER

**CTMB4001LS**



CT Mounting Base accommodates the preference difference between line and load connections inside a CT cabinet. The bases are available in three variations of conductor connection styles to match your application: 1/2-in. studs on 1-3/4-in. centers, a model with mechanical lugs and a model with lugs on one side and studs on the other. Pre-punched mounting base holes align with the studs in a CT cabinet

## INDUSTRY STANDARDS

UL 414 Listed; File E240312

## FEATURES

Spacing for bar-type current transformer that conforms to ANSI 12.11

Conductor provisions: either mechanical lugs or 1/2-in. bolt on 1-3/4-in. centers with nut, spring and flat washer

Neutral bar with 10-32 tap screw

12-gauge galvanized formed base has electrically isolated mount/termination platform

## PRODUCT ATTRIBUTES

Article Number: 15641

Material: Mild Steel

Finish: Galvanized; Powder Coated

Thickness: 2.05mm

Connection Type: Lugs; Studs

AIC (Ampere Interrupting Capacity) Rating: 50000A

Current: 400A

Max Voltage AC: 600V

Wire Size: (3) 750 MCM - 1/0; (6) 250 MCM - 1/0

Service Type: 1Ø3W

CT Provision Quantity: 2

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**