

ZonEx ATEX- and IECEx-Certified Type 4X Screw Cover, 8.5x5.75x5, Brushed, Stainless 316

CATALOG NUMBER

EXE965SS6

Zonex Enclosures are designed and certified to meet ATEX Directive 2014/35/EU as well as IECEx standards for increased safety in housing electrical components in Zone 1 and Zone 2 applications. HOFFMAN's ATEX Ex e enclosures are not intended for use in explosion-proof or flame-proof applications.

INDUSTRY STANDARDS

Type 4, 4X, 12; File No. E61997

cUL G22.2 No. 94 Listed; Type 4, 4X, 12; File No. E61997

ATEX Directive 2014/34/EU

ATEX

Sira 09ATEX3224U

2813 Ex II 2 G D

Ex eb Gb

Ex tb IIIC Db IP 66

EN60079-0

EN60079-7

EN60079-31

IECEx

IECEx SIR 09.0099U

Ex eb IIC Gb

Ex tb IIIC Db IP 66

IEC 60079-0

IEC 60079-7

IEC 60079-31

NEMA/EEMAC Type 4, 4X, 12

IEC 60529, IP66



FEATURES

6 mm brass internal/external bonding provision

One piece continuous gasket on door

Type 316L stainless steel cover screws

Mounting panel and hardware for bonding provisions included

Operating temperature range: -40°C to +70°C standard polyurethane gasket

Internal weldstuds for panel or DIN rail mounting brackets

3-mm thick individual welded-on top and bottom wall-mounting brackets

Increased safety: Ex e. IECEx e certified

PRODUCT ATTRIBUTES

Article Number: 21473

Height: 8.5in

Width: 5.75in

Depth: 5in

Material: Stainless Steel 316L

Finish: Brushed 320 grain

Thickness: 16ga

Weight: 4lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE