

Deep-Hinged Window Kit for InLine HMI, fits 250x250mm, Smooth, Polycarbonate

CATALOG NUMBER

LWHD2525



Clear molded polycarbonate window has a 31.8-mm (1.25-in.) clear space between enclosure front opening and window surface. Space also accommodates equipment mounted on optional front plate. Die-cast backing plate has a black polyester powder finish. This kit can be used as an accessory window kit on other HOFFMAN enclosures.

FEATURES

Includes mounting hardware for window and optional front plate

Window kit is hinged on left side with a 140-degree door opening and a quarter-turn slotted latch

Purchase Front Plate separately

PRODUCT ATTRIBUTES

Article Number: 49920

Height: 9.84in

Width: 9.84in

Depth: 1.64in

Material: Polycarbonate

Finish: Smooth Matte

Thickness: 0.12in

Window Size: 8.78 x 7.97in

Weight: 2.6lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE