



Locking Devices, Bryant Power Interrupting, Flanged Inlet, 30A 3-Phase Delta 480V AC, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted

By Bryant
Catalog # 20418

Locking Devices, Bryant Power Interrupting, Flanged Inlet, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating Description	20 Amp /30 Amp
Current Rating	20A/30 A
Amperage Rating	20A/30 A



Voltage Rating Description	250 VDC/600 VAC
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 VDC/600 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.94 in
Height	1.75 in
Dimensions	3.28 in x 1.94 in x 1.75 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Color	Aluminum
Item Type	20A/30A Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786618527

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)