


# Thermoelectric Temperature Controller, 3.19x6.5x.05, 48VDC, Printed Circuit Board

## CATALOG NUMBER

**TEC48VCNTRLRN**



Thermoelectric Temperature Controller printed circuit board provides PWM (Pulse-Width-Modulation) regulation of cooling and heating output for TEC units.

## FEATURES

Provides PWM (Pulse-Width-Modulation) regulation of cooling and heating output for TEC units

Automatically switches between cooling and heating

4 cooling temperature set points range from 22.5 C to 35 C (35 C Factory Setting)

3 heating temperature set points range from -5 C to 15 C (15 C Factory Setting)

Heating function can be easily disabled if desired

On-board LEDs indicate low temp, high temp alarm, and overall system status

Dry contact relay output provides for external alarm indication

## PRODUCT ATTRIBUTES

Article Number: 27637

Height: 3.19in

Width: 6.5in

Depth: 0.05in

Weight: 1.6lb

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**