



Straight Blade Devices, Receptacles,
Hospital Grade QUADPLEX Receptacle,
Surge Suppression, Isolated Ground, 20A
125V, 2-Pole 3-Wire Grounding, 5-20R

By Bryant
Catalog # [21254HSA](#)

Straight Blade Devices, Receptacles, Hospital Grade QUADPLEX
Receptacle, Surge Suppression, Isolated Ground, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R, Blue

Features

- Hospital Grade QUADPLEX Receptacle
- Surge Suppression
- Isolated Ground
- 20A 125V
- 2-Pole 3-Wire Grounding

Application

Quad-Plex

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Configuration

Number Of Outlets	4
-------------------	---

Current

Current Rating	20 A
Amperage Rating	20 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Terminal Screws
Wattage	2500 W
Voltage Rating	125 V



Dimensions

Display Size	Standard Sized Product
Length	4.3 in
Width	4.30 in
Weight	0.5 lb.
Height	0.92 in
Dimensions	4.3 in x 4.30 in x 0.92 in

General

Series	Hospital Grade
OEM Brand Name	Hubbell Bryant
Outlet	Straight Blade
Color	Blue
Item Type	Smooth Face
Material - Mounting Hardware	Screw Mounting
Type	Four Outlet Receptacle
Material	Composite
UPC	781786190269

Logistics

Carton Quantity	10
-----------------	----

Operational

Response Time	5
Indicator(s) Type	LED Visual Status Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)