

# ClimaGuard Air-to-Water Heat Exchanger Indoor, 879w 200-250v

## CATALOG NUMBER

**WCHE01926002**



Air-to-Water Indoor Heat Exchanger removes heat from an enclosure by flowing enclosure hot air across a water-cooled exchanger core. Inside cabinet temperatures can range from 10-50 C (50-122 F) while ambient operating temperatures can range from 10-70 C (50-158 F). Includes a condensation recovery system and condensation discharge pipe. These units require an available cooled water source.

## INDUSTRY STANDARDS

UL/cUL Listed; Type 12; File No. SA33866

CE

EAC (230V models only)

IP55/IP54 (reference item technical data)

## FEATURES

Filterless, refrigerant-less design

NEMA power cord connection standard

Copper pipe and aluminum fins heat exchanger core

Air movers with thermal protection

Regulating mechanical thermostat set at 35 C (95 F), differential of 4 C (7 F)

Solenoid water valve

## PRODUCT ATTRIBUTES

Article Number: 25613

Capacity Watts @  $\Delta t$  25°C: 870W

Capacity Btu/h @  $\Delta t$  25°C: 2968Btu/h

Nominal Voltage: 230V

Height: 15.9in

Width: 12.12in

Depth: 4.49in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Weight: 20lb

Thickness: 18ga

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**