



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 30A 250V DC/600V AC, Non-NEMA

By Bryant
Catalog # 21414

Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	4-Wire Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Ampereage Rating Description	20 Amp /30 Amp
Current Rating	20A/30 A
Ampereage Rating	20A/30 A
Voltage Rating Description	250 VDC/600 VAC
Connectivity	Pressure Terminal Screws



Voltage Rating	250 VDC/600 VAC
Dimensions	
Display Size	Standard Sized Product
Length	2.44 in
Width	2.44 in
Height	6.00 in
Dimensions	2.44 in x 2.44 in x 6.00 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Color	Black, White
Item Type	20A/30A Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786618602

Logistics

Carton Quantity	5
-----------------	---

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)