



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Side Wired Only, With NEMA 1 Enclosure

By Bryant
Catalog # 30102D

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Side Wired Only, Black, With NEMA 1 Enclosure



Features

- Toggle
- Motor Disconnects
- Double Pole
- 30A 600V AC
- Side Wired Only

Application

Standard Toggle

Specifications

Environmental Conditions	Indoor Only
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

Conductor

Number Of Poles	2 Pole
-----------------	--------

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	600V AC kV
Phase	Single Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	18000
Voltage Rating	600V AC kV

Dimensions

Display Size Standard Sized Product

Force Related

Load Capacity Inductive

General

Enclosure Type	NEMA 1
Series	Non-Fused
OEM Brand Name	Hubbell Bryant
Style	Standard Duty
Item Type	Enclosed Switch
Material - Mounting Hardware Type	Screw Mounting Disconnect Switches
UPC	781786631557

Logistics

Carton Quantity	10
Pallet Quantity	880

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)