



Locking Devices, Locking Devices,
Industrial, Flanged Inlet, 50A 250V
DC/600V AC, 3-Pole 4-Wire Grounding,
Non-NEMA, Screw Terminal, Galvanized

By Bryant
Catalog # 3768

Locking Devices, Locking Devices, Industrial, Flanged Inlet, 50A
250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw
Terminal,Galvanized

Features

- Flanged Inlet with Lift Cover and Gasket
- 50A 250V DC/600V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	250 VDC/600 VAC
Connectivity	Pressure Terminal Screws
Voltage Rating	250 VDC/600 VAC



Dimensions

Display Size	Standard Sized Product
Length	2.77 in
Width	3.50 in
Height	3.50 in
Dimensions	2.77 in x 3.50 in x 3.50 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Metallic
Item Type	50A Male Flanged Inlet-For Replacement Use
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786652750

Logistics

Carton Quantity	5
-----------------	---

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)