



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant
Catalog # [23002G](#)

Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 20A 125V/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Heavy Duty Industrial

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator Yes

Conductor

Number Of Wires 3-Wire
Wire Size #16 AWG to #12 AWG
Number Of Conductors 3-Wire Grounding
Conductor Range #14 AWG to #12 AWG
Number Of Poles 2-Pole

Current

Current/Amperage Rating 20 Amp/10 Amp
Description
Current Rating 10A/20 A
Amperage Rating 10A/20 A
Voltage Rating Description 125 VAC/125 VDC/250 VDC/480 VDC
Connectivity Pressure Terminal Screws



Voltage Rating 125 VAC/125 VDC/250 VDC/480 VDC

Dimensions

Display Size Standard Sized Product
Length 1.62 in
Width 1.62 in
Height 3.56 in
Dimensions 1.62 in x 1.62 in x 3.56 in

General

OEM Brand Name Hubbell Bryant
Style Grounding
Color Black, White
Item Type 10A/20A Connector
Insulation Insulated Body
Material - Mounting Hardware Cord Mounted Connector Body
Type Composite
Material Composite
UPC 781786618831

Logistics

Carton Quantity 20

Operational

Temperature Rating

- Maximum Continuous: 75° C
- Minimum Continuous: -40° C w/o impact, -25° with impact.

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)