



**Straight Blade Devices, Equipment Base
Devices - Clamp Type, Back Wiring, Male Self
Grounding Strap, Industrial/Commercial, 15A
125V, 5-15P**

By Bryant
Catalog # [5278G](#)

Straight Blade Devices, Equipment Base Devices - Clamp Type, Back
Wiring, Male Self Grounding Strap, Industrial/Commercial, 15A 125V, 2-
Pole 3-Wire Grounding, 5-15P, Black, Single Pack

Features

- Back Wiring
- Male Self Grounding Strap
- Industrial/Commercial
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	5-15P


Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 3000V Minimum in
Current Rating	15 A
Voltage Rating	125 V
Wattage	1875
Connectivity	Screw Terminals
Current / Amperage Rating	15 A

Dimensions



Length	1.84 in
Display Size	Standard Sized Product
Weight	0.1 lb.
Height	1.55 in
Width	2.50 in
Dimensions	1.84 in x 2.50 in x 1.55 in

General

Color	Black
Style	Clamp Type
Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
UPC	781786625174
Type	Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Insulation	Insulated Body
Item Type	Single Flanged

Logistics

Carton Quantity	100
-----------------	-----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)