



# Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 30A 250V DC/600V AC, Non-NEMA

By Bryant  
Catalog # 25414



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 30A 600V AC/ 20A 250V DC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black nylon with cord grip

## Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

## Application

Heavy Duty Industrial

## General

Catalog Number	25414
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A/30A Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Style	Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786683952

## Dimensions

Dimensions	2.69 in x 2.69 in x 6.78 in
Display Size	Standard Sized Product
Height	6.78 in
Length	2.69 in
Width	2.69 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current Rating	30 A
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding
Wire Size	#18 AWG to #8 AWG

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 25414 Specification Sheet English](#)
- [Specifications - 25414 Specification Sheet French](#)