



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant
Catalog # 26422

Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 60A 600V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Yellow

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Color coded metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	60 Amp
Description	
Current Rating	60 A
Amperage Rating	60 A
Voltage Rating Description	600V AC
Connectivity	Pressure Terminal Screws



Voltage Rating	600 VAC
Dimensions	
Display Size	Standard Sized Product
Length	4.12 in
Width	4.12 in
Height	3.95 in
Dimensions	4.12 in x 4.12 in x 3.95 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Color	Yellow
Item Type	60A Single Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786584228

Logistics

Carton Quantity	5
-----------------	---

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)