



Locking Devices, Locking Devices,
Industrial, Female Connector Body, 50A
250V DC/600V AC, 3-Pole 4-Wire
Grounding, Non-NEMA, Screw Terminal and
White

By Bryant
Catalog # 3764

Locking Devices, Locking Devices, Industrial, Female Connector
Body, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-
NEMA, Screw Terminal, Black and White

Features

- Female Connector Body
- 50A 250V DC/600V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	4-Wire Grounding
Conductor Range	#6 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	250 VDC/600 VAC
Connectivity	Pressure Terminal Screws
Voltage Rating	250 VDC/600 VAC



Dimensions

Display Size	Standard Sized Product
Length	6.50 in
Width	2.56 in
Height	2.56 in
Dimensions	6.50 in x 2.56 in x 2.56 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Heavy Duty Connector-For Replacement Use
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786652552

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)