



Locking Devices, Industrial, Flanged Inlet,
20A 250V, 2-Pole 3-Wire Grounding, L6-
20P, Screw Terminal, White, With
Weatherproof Cover

By Bryant
Catalog # 70620MBWP

Locking Devices, Industrial, Flanged Inlet, 20A 250V, 2-Pole 3-
Wire Grounding, L6-20P, Screw Terminal, White, With
Weatherproof Cover

Features

- Flanged Inlet
- 20A 250V
- 2-Pole 3-Wire Grounding
- L6-20P
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	Yes
Nema Rating	L6-20P

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250 V
Connectivity	Screw Terminals
Voltage Rating	250 V



Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Weatherprotective
Color	White
Item Type	20A Weather Protective Power Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786689275

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)