



Locking Devices, Locking Devices,
Industrial, Flanged Inlet, 15A 125V, 2-Pole3-
Wire Grounding, L5-15P, Screw Terminal,
White

By Bryant
Catalog # 4716MB

Locking Devices, Locking Devices, Industrial, Flanged Inlet, 15A
125V, 2-Pole3-Wire Grounding, L5-15P, Screw Terminal, White

Features

- Flanged Inlet
- 15A 125V
- 2-Pole3-Wire Grounding
- L5-15P
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L5-15P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125V
Connectivity	Screw Terminals
Voltage Rating	125 V



Dimensions

Display Size	Standard Sized Product
Length	1.84 in
Width	2.50 in
Height	1.68 in
Dimensions	1.84 in x 2.50 in x 1.68 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	15A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786405202

Logistics

Carton Quantity	10
Pallet Quantity	2080

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)