



Locking Devices, Industrial, Flanged Inlet,
30A 480V AC, 2-Pole 3-Wire Grounding,
L8-30P, Screw Terminal, Black and White

By Bryant
Catalog # 70830MB

Locking Devices, Industrial, Flanged Inlet, 30A 480V AC, 2-Pole
3-Wire Grounding, L8-30P, Screw Terminal, Black and White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L8-30P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3500V
Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	480V AC
Connectivity	Screw Terminals
Voltage Rating	480 VAC



Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	Black, White
Item Type	30A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Flanged Inlet
Material	Composite
UPC	781786691162

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)