



Locking Devices, Industrial, Flush Receptacle, 20A 600V AC, 2-Pole 3-Wire Grounding, L9-20R, Screw Terminal, Black

By Bryant
Catalog # [70920FR](#)

Locking Devices, Industrial, Flush Receptacle, 20A 600V AC, 2-Pole 3-Wire Grounding, L9-20R, Screw Terminal, Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

EU RoHS Indicator Yes
Nema Rating L9-20R
Standards - RoHS Compliance CM
Status

Conductor

Number Of Wires 3-Wire
Wire Size #14 AWG to #8 AWG
Number Of Poles 2-Pole

Current

Phase Single Phase



Current/Amperage Rating	20 Amp
Description	
Connectivity	Terminal Screws
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	600V AC
Voltage Rating	600 VAC

Dimensions

Display Size	Standard Sized Product
Width	1.70 in
Height	1.24 in
Length	3.28 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

Item Type	20A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786691636
Style	Single Receptacle

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)